



## USB to Serial Converter

ICUSB232\_2

ICUSB232\_4

Thank you for purchasing a StarTech.com USB to serial interface converter. Now you can turn one of your computer's USB ports into multiple RS-232 serial ports. The adapter is powered through the USB bus so no external power source is needed.

### Features

- Offers fast transfer rates of up to 1.5 Mbits/sec
- Turns one USB port into multiple DB-9 RS-232 serial ports
- Works with cellular phones, PDAs, digital cameras, modems, and ISDN terminal adapters
- Supports remote wake-up and power management
- Frees your RS-232 ports for other uses
- Powered through USB bus so no external power adapter is needed

### Before You Begin

#### System Requirements

- Computer running Windows 98/98SE/Me/2000/XP, Mac 8.6 and up, or Linux 2.40 and up
- The system must be equipped with USB Host Controller

#### Contents

- 1 x USB to Serial converter
- 1 x Driver disk

### Installation

**Note:** Depending on your operating system and the configuration of your system, the following instructions may not be identical to what you see on your screen.

1. Plug your serial device into one of the serial ports on the converter. Plug the converter's USB cable into an open USB port on your computer.
2. The New Hardware Wizard will appear. Click **Next**.
3. Choose "Search for the best drivers for your device" and click **Next**.
4. Insert your driver disk into the disk drive. Make sure the proper drive is checked then click **Next**.
5. Click **Next**, then **Finish** to complete the installation.

You may have to go through the driver installation process for each port individually (i.e., twice for the two-port converter).

#### To Change Your Serial Devices

To change the serial devices connected to your converter, just plug in the new device and press the **Reset** button (located on the converter) for that port. Your system will automatically detect the new device.

### Technical Specifications

<b>Interface</b>	USB to Serial
<b>Standard</b>	USB V1.1
<b>Data Transfer Rate</b>	<b>USB:</b> Up to 12 Mbits/sec <b>Serial:</b> Up to 1.5 Mbits/sec
<b>OS Compatibility</b>	<b>Windows</b> 98SE/ME/2000 & XP, <b>Mac OS</b> 8.6 & up, <b>Linux</b> Version 2.40 & up
<b>Connectors</b>	Upstream: USB Type A (Male) Serial: DB-9 Pin (Male)
<b>Power</b>	Bus Powered
<b>USB Cable Length</b>	2ft (0.6m)
<b>Safety Standards</b>	FCC & CE

### Warranty Information

This product is backed by a one-year warranty. In addition, StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

#### Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product.

Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.

Call StarTech.com tech support for help:

USA/Canada: 1-800-265-1844

UK/Ireland/Europe: 00-800-7827-8324

Support hours: Monday to Friday 9:00AM to 5:00PM EST (except holidays)