

Composite/S-Video to HDMI Video Converter with Audio

VID2HDCON



*actual product may vary from photos

DE: Bedienungsanleitung - de.startech.com

FR: Guide de l'utilisateur - fr.startech.com

ES: Guía del usuario - es.startech.com

IT: Guida per l'uso - it.startech.com

NL: Gebruiksaanwijzing - nl.startech.com

PT: Guia do usuário - pt.startech.com

For the most up-to-date information, please visit: www.startech.com

FCC Compliance Statement

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. Regardless of any direct acknowledgement elsewhere in the body of this document, StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

Table of Contents

| | |
|-----------------------------------|----------|
| Introduction | 1 |
| Packaging Contents | 1 |
| System Requirements..... | 1 |
| Front View | 2 |
| Rear View..... | 2 |
| Side View | 3 |
| Installation | 4 |
| Hardware Installation | 4 |
| Driver Installation..... | 4 |
| Specifications | 6 |
| Technical Support | 7 |
| Warranty Information | 7 |

Introduction

The VID2HDCON Composite and S-Video to HDMI® Video Converter with Audio lets you connect an S-Video or Composite device with supporting 3.5mm audio to your HDMI monitor or television.

Equipped with convenient selector switches for configuration, the S-Video/composite converter is able to function in both NTSC and PAL systems, and offers support for output resolutions up to 1600x1200 (PC) or 1080p (TV) to seamlessly integrate with almost any display.

An integrated 3.5mm audio connection provides the ability to send your output through a single HDMI cable to your destination display, avoiding the hassle of running a separate audio cable.


Packaging Contents

- 1 x Video Converter
- 1 x Universal Power Adapter
- 3 x Power Adapter plug (NA/UK/EU)
- 1 x Instruction Manual


System Requirements

- Composite or S-Video enabled video source (i.e. DVD player, PVR/DVR, etc.)
- Composite or S-Video cable
- HDMI enabled display device (e.g. monitor, projector, etc.)
- HDMI cable
- Available AC electrical outlet


Front View



Rear View



Side View



Installation

Hardware Installation

1. Make sure all devices and components are powered off.
2. Connect the video source to the input side of the video converter using either an S-Video or composite RCA cable (both sold separately).
3. For audio, connect a 3.5mm Audio mini-jack cable into the "Audio In" connector on the converter. Audio will be combined and output through HDMI.
4. Plug the power adapter into the video converter. The Input indicator LED will light up steady.
5. If not already set to the correct input, press the Input selector button to change the input source. The LED will light up green for composite and red for S-Video.
6. Connect the display to the converter using a male/male HDMI cable (sold separately).
7. Set the Output Signal Mode selector switch along the side of the video converter to the type of display you are using: "HD" for a TV and "PC" for a monitor.
8. Select the output resolution using the slide switch next to the HDMI output connector. Make sure to select an output resolution that is supported by the display device.
9. Power on the display device.
10. Power on the video source.

Driver Installation

The video converter is an external pure hardware converter, so no driver or software installation is required.

Specifications

| | |
|--------------------------------|---|
| Video Signal (Input) | Composite S-Video |
| Video Signal (Output) | HDMI |
| Connectors | 1 x RCA Composite female 1 x S-Video 4-pin female 1 x HDMI type A female 1 x DC Power |
| LEDs | 1 x Input Selection |
| Supported Video Systems | NTSC, PAL |
| Supported Video Output | PC: XGA (1024x768), SXGA (1280x1024), UXGA (1600x1200) @ 60 Hz HD: 480p, 720p, 1080p @ 50/60 Hz |
| On Screen Display | Yes |
| Audio Support | Yes |
| Power Adapter | 5V DC, 1.2A, center positive, type M plug |
| Enclosure Material | Plastic |
| Operating Temperature | 0°C ~ 40°C (32°F ~ 104°F) |
| Storage Temperature | -20°C ~ 60°C (-4°F ~ 140°F) |
| Humidity | 20% ~ 90% RH |
| Dimensions (LxWxH) | 165.0mm x 162.6mm x 33.5mm |
| Weight | 100g |

Technical Support

StarTech.com's lifetime technical support is an integral part of our commitment to provide industry-leading solutions. If you ever need help with your product, visit www.startech.com/support and access our comprehensive selection of online tools, documentation, and downloads.

For the latest drivers/software, please visit www.startech.com/downloads

Warranty Information

This product is backed by a two year warranty.

In addition, StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.

Hard-to-find made easy. At StarTech.com, that isn't a slogan. It's a promise.

StarTech.com is your one-stop source for every connectivity part you need. From the latest technology to legacy products — and all the parts that bridge the old and new — we can help you find the parts that connect your solutions.

We make it easy to locate the parts, and we quickly deliver them wherever they need to go. Just talk to one of our tech advisors or visit our website. You'll be connected to the products you need in no time.

Visit www.startech.com for complete information on all StarTech.com products and to access exclusive resources and time-saving tools.

StarTech.com is an ISO 9001 Registered manufacturer of connectivity and technology parts. StarTech.com was founded in 1985 and has operations in the United States, Canada, the United Kingdom and Taiwan servicing a worldwide market.

Reviews

Share your experiences using StarTech.com products, including product applications and setup, what you love about the products, and areas for improvement.

StarTech.com Ltd.

45 Artisans Crescent
London, Ontario
N5V 5E9
Canada

StarTech.com LLP

4490 South Hamilton
Road
Groveport, Ohio
43125
U.S.A.

StarTech.com Ltd.

Unit B, Pinnacle 15
Gowerton Road
Brackmills,
Northampton
NN4 7BW
United Kingdom

StarTech.com Ltd.

Siriusdreef 17-27
2132 WT Hoofddorp
The Netherlands

FR: fr.startech.com

DE: de.startech.com

ES: es.startech.com

NL: nl.startech.com

IT: it.startech.com

JP: jp.startech.com