

## 42U 2 Post Open Frame Rack with Casters

2POSTRACK

DE: Bedienungsanleitung - de.startech.com  
 FR: Guide de l'utilisateur - fr.startech.com  
 ES: Guía del usuario - es.startech.com  
 IT: Guida per l'uso - it.startech.com  
 NL: Gebruiksaanwijzing - nl.startech.com  
 PT: Guia do usuário - pt.startech.com

**WARNING!** To prevent bodily injury, please ensure that the rack is installed in a structurally sound environment with a level floor and that all hardware has been assembled securely, and checked for stability before loading equipment. When installing equipment into the rack, start from the bottom of the rack first and move upwards, keeping the heaviest equipment at the bottom to avoid a situation where the rack becomes top-heavy.

### Installation



1. Place the top (part with the DuraRak symbol), bottom, and each side post of the 2POSTRACK on the ground for positioning of alignment.



2. When the panels are aligned, the holes should match up with each other allowing you to use the Allen Key to fasten each corner with the nuts and bolts provided.
3. Once one side of the 2POSTRACK is fastened please flip the rack over and follow the instructions in Step 2.



4. Attach the casters, which are included with the packaging, to the legs of the 2POSTRACK. Use a Phillips screwdriver and screws to mount the casters to the legs of the unit.



\*actual product may vary from photos



5. Mount the legs to the base of the rack and attach them with the screws and nuts. Use the Allen key to fasten the nuts and screws and stand the rack up.
6. Using the rackmount screws and cage nuts, install your rackmount equipment in the 2POSTRACK.

## **Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols**

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. Regardless of any direct acknowledgement elsewhere in the body of this document, StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

## **Technical Support**

StarTech.com's lifetime technical support is an integral part of our commitment to provide industry-leading solutions. If you ever need help with your product, visit [www.startech.com/support](http://www.startech.com/support) and access our comprehensive selection of online tools, documentation, and downloads.

For the latest drivers/software, please visit [www.startech.com/downloads](http://www.startech.com/downloads)

## **Warranty Information**

This product is backed by a lifetime warranty.

In addition, StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

## **Limitation of Liability**

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.