



Cat 5e Cable (Snagless)

45PATXXMY



Marking: **CAT.5E UTP PATCH ETL/3P VERIFIED TO ANSI/TIA-568-C.2 & ISO/IEC 11801 ED.2 & EN 50288-3-2 & IEC 60332-1-2 ▲ 24AWGX4P CM(UL) c(UL) E164469-XX**



NOTE:
 1.ELECTRICAL TEST:
 <1> 100% OPEN SHORT & MISS WIRE TEST.
 <2> INSULATOR RESISTANCE:DC300V 10Mohm MIN.
 <3> CONNECTOR RESISTANCE: 2 ohm MAX

PINOUT			
P1(T568B)		P2(T568B)	WIRE
1	[Crossed]	1	WHT/ORG
2		2	ORG
3	[Crossed]	3	WHT/GRN
6		6	GRN
4	[Crossed]	4	BLU
5		5	WHT/BLU
7	[Crossed]	7	WHT/BRN
8		8	BRN

Part No.	Color	Length	Tolerance
45PAT50CMyy	BK/BL/GR/GN/RD/OR/YL/WH	50CM	±15mm
45PAT1Myy	BK/BL/GR/GN/RD/OR/YL/WH	1M	±15mm
45PAT2Myy	BK/BL/GR/GN/RD/OR/YL/WH	2M	±15mm
45PAT3Myy	BK/BL/GR/GN/RD/OR/YL/WH	3M	+15mm/-20mm
45PAT5Myy	BK/BL/GR/GN/RD/OR/YL/WH	5M	+15mm/-20mm
45PAT7Myy	BK/BL/GR/GN/RD/OR/YL/WH	7M	+40mm/-20mm
45PAT10Myy	BK/BL/GR/GN/RD/OR/YL/WH	10M	+40mm/-20mm
45PAT15Myy	BK/BL/GR/GN/RD/OR/YL/WH	15M	+50mm/-20mm

Conductor	Bare Copper 24AWG 7/0.196±0.08mm		
Insulation	Thickness:MIN at any point:0.15mm MAX AVG:0.25mm Diameter:0.98±0.06mm		
Jacket	CM	Thickness:MIN at any point:0.42mm MAX AVG:0.48mm Diameter:5.6±0.2mm	
Wire	CAT. 5E UTP STR 24AWGX4P		
Plug	YU-14 8P8C 50U"		