


No	Part	Material / color
(1)	LC dust cap	TPV / white
(2)	LC housing	PEI / beige
(3)	LC duplex clip	PEI / beige
(4)	LC boot 1	TPV / red
(5)	LC boot 2	TPV / black
(6)	LC ferrule	Ceramic
(7)	ST dust cap	LDPE / white
(8)	ST housing	Zinc alloy
(9)	ST boot 1	TPV / red
(10)	ST boot 2	TPV / black
(11)		Ceramic

No	Part	Material / color
A	OM2 fiber	Glass
B	Buffer 1	LSZH / white
C	Buffer 2	LSZH / orange
D	Yarn	Kevlar / yellow
E	Jacket	LSZH / orange

SKU	Length (m)
50FIBLCST1	1
50FIBLCST2	2
50FIBLCST5	5
50FIBLCST10	10

THIRD ANGLE PROJECTION



GENERAL NOTES

DIMENSIONS ARE IN MM - DO NOT SCALE
 THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM

StarTech.com

PRODUCT ID	50FIBLCSTxx
DESCRIPTION	Fiber Optic Cable - Multimode Duplex 50/125 - LSZH - LC/ST
DO NOT SCALE	SHEET: 1 OF: 1
	UPLOAD DATE: 4/05/2023