


# Cat6a Patch Cable - Shielded

6ASPATxxMyy



P/N	COLOR: yy	LENGTH(xx)
6ASPAT5Myy	GR/BL/BK/GN/RD/YL/OR/PL/WH/AQ	5000+40/-0mm
6ASPAT7Myy	GR/BL/BK/GN/RD/YL/OR/PL/WH/AQ	7000+40/-0mm
6ASPAT10Myy	GR/BL/BK/GN/RD/YL/OR/PL/WH/AQ	10000+80/-0mm

PINOUT:

P1	COLOR	P2
1	WHITE/ORANGE	1
2	ORANGE	2
3	WHITE/GREEN	3
4	BLUE	4
5	WHITE/BLUE	5
6	GREEN	6
7	WHITE/BROWN	7
8	BROWN	8
SHELL	DRAIN	SHELL

## SPEC:

- CABLE:CM TYPE CM 26AWG 75°C(UL) E132276-A CSA LL64151-A VERIFIED EIA/TIA-568  
-B.2-10 STP CAT.6A 4PR 1G JACKET PVC COLOR: yy OD:6.3mm (PRINTING " StarTech.com " )
- CONNECTOR:CAT6A RJ45, 8P8C LONG TELEPHONE PLUG METAL SHELL  
(SHELL:GOLD FLASH,PIN:GOLD PLATED)
- MOLDING PVC COLOR:yy