


Electrical Test:

- 100%Test(Open ,short ,miss wire);
- Contact Resistance: \* ohm(max);
- Insulation Resistance: DC 300V/10ms,10M ohm(MIN);

11	Tube~1.5mm
10	Tube~2.5MM
9	DisplayPort M~Boarding Cap
8	Copper foil~25u~W=25MM
7	DisplayPort M~lower Shell~Black~PC+ABS
6	DisplayPort M~upper Shell~Black~PC+ABS
5	TPE~45P~Black
4	LDPE
3	DisplayPort M~Clamp
2	DisplayPort M~Connector~Insulator Black~Pin Gold plated~Shell Gold plated
1	[26AWG(7/0.16BC)+EAM]*5P+26AWG(7/0.16TC)*4C+AEB(16/11/0.12 85%AL)~OD:8.5MM~TPE~jacket colour:black.Jacket printing: DisplayPort Cable E342987 AWM STYLE 21572 80°C 30V VW-1
NO	DESCRIPTION

Part Number	Length(mm)
DISPLPORT20L	6100 <sup>+40</sup> <sub>0</sub>
DISPL7M	7000 <sup>+40</sup> <sub>0</sub>
DISPLPORT25L	7625 <sup>+80</sup> <sub>0</sub>

THIRD ANGLE PROJECTION



GENERAL NOTES

DIMENSIONS ARE IN MM - DO NOT SCALE

THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM

StarTech.com

PRODUCT ID	DISPLPORT(20-7M-25)L		
DESCRIPTION	DisplayPort Cable - 2560 x 1440p		
DO NOT SCALE	SHEET: 1 OF: 1	UPLOAD DATE: 4/03/2025	