


**CONTACT LAYOUT**

#P1	#P2	#P1	#P2
3 — Blue	10 — Blue	12 — Blue	1 — Blue
1 — White	12 — White	10 — White	3 — White
2 — Drain	11 — Drain	11 — Drain	2 — Drain
6 — Blue	7 — White	15 — White	15 — White
4 — White	9 — Blue	17 — Blue	17 — Blue
5 — Drain	8 — Drain	16 — Drain	16 — Drain
9 — Blue	4 — Red	16 — Red	16 — Red
7 — White	13 — Orange	13 — Orange	13 — Orange
8 — Drain	14 — Yellow	14 — Yellow	14 — Yellow
	18 — Blue	18 — Blue	18 — Blue
	19 — Black	19 — Black	19 — Black
	20 — Braid	20 — Braid	20 — Braid
	Shell	Shell	Shell

Part. NO	L(mm)	T(mm)
DP14A-7M-DP	7000	±100
DP14A-10M-DP	10000	±150
DP14A-15M-DP	15000	±200

THIRD ANGLE PROJECTION



**GENERAL NOTES**

DIMENSIONS ARE IN MM - DO NOT SCALE  
 THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM



PRODUCT ID	DP14A-xxM-DP-CABLE		
DESCRIPTION	Active DisplayPort 1.4 Cable		
<b>DO NOT SCALE</b>	<b>SHEET: 1 OF: 1</b>	<b>UPLOAD DATE: 4/28/2026</b>	