




Wire Pin Assignment and Wire Description.

CN.1	PAIR#	CN.2	COLOR
11	PAIR1	1	DRAIN
12		3	WHITE
10		5	BLUE
8	PAIR2	7	DRAIN
9		9	WHITE
7		11	BLUE
5	PAIR3	13	DRAIN
6		15	WHITE
4		17	BLUE
19	SIGNAL	19	BLUE
18	SIGNAL	2	RED
13	SIGNAL	4	GREEN
14	SIGNAL	6	PURPLE
2	PAIR4	8	DRAIN
3		10	WHITE
1		12	BLUE
16	PAIR5	14	DRAIN
15		16	WHITE
17		18	YELLOW
SHELL		SHELL	BRAID

Part Number	Length (L)
DP14MDPMM1MB	1000±30mm
DP14MDPMM2MB	2000±50mm

MOLDING:PVC BLACK

Mini DISPLAYPORT 20PIN PLUG,TERMINAL Au-PLATED SHELL Au-PLATED

DISPLAYPORT TOP/LOWER CASING:PC BLACK

DISPLAYPORT 20PIN PLUG,TERMINAL Au-PLATED SHELL Au-PLATED

DP CABLE [(34AWGx2C+EAM)x5P+34AWGx4C]+AB OD:4.5 BLACK PVC

MATERIALS LIST & SPEC. DESCRIPTION

5

4


3

2

1

ITEM NO.

THIRD ANGLE PROJECTION



GENERAL NOTES

DIMENSIONS ARE IN MM - DO NOT SCALE
THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM

StarTech.com

PRODUCT ID DP14MDPMMxMB

DESCRIPTION VESA Certified Mini DisplayPort to DisplayPort 1.4 Cable

DO NOT SCALE SHEET: 1 OF: 1 UPLOAD DATE: 2/21/2023