



PIN Assignment

| P2 | P1 | P3 |
|--------|--------|----|
| 1 — BK | 1 — BK | 1 |
| 2 — RD | 2 — RD | 2 |
| 3 — YL | 3 — YL | 3 |
| 4 — BL | 4 — BL | 4 |

ELECTRICAL TESTING:
 (1)100% open short &miss wire test.
 (2)Insulation Resistance:≥5MΩ.
 (3)Contact Resistance:≤5Ω.
 (4)Dielectric Strength:DC 200V/0.1s.

| ③ | 4P PWM FAN CONNECTOR PLUG,TIN-PLATED TERMINAL | 1 |
|------|--|-----|
| ② | 4P PWM FAN CONNECTOR RECEPTACLE,TIN-PLATED TERMINAL | 2 |
| ① | FLAT CABLE 28AWG, 7C*0.12TC*4C,JACKET,PVC,5.0*1.3mm ,BK/RD/YL/BL | 2 |
| ITEM | DESCRIPTION | QTY |

THIRD ANGLE PROJECTION

GENERAL NOTES
 DIMENSIONS ARE IN MM - DO NOT SCALE
 THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM

StarTech.com

| | |
|-------------------------------|---|
| PRODUCT ID | FAN4SPLIT12 |
| DESCRIPTION | 12in 4 Pin Fan Power Splitter Cable - F/M |
| DO NOT SCALE | SHEET: 1 OF: 1 |
| UPLOAD DATE: 3/03/2022 | |