




P1




P2

PINOUT:

P1	1	BLUE	TERMINATOR
	2	ORANGE	TERMINATOR
	3	BLACK	TERMINATOR
	4	RED	TERMINATOR
	5	GREEN	TERMINATOR
	6	YELLOW	TERMINATOR
	7	BROWN	TERMINATOR
	8	WHITE	TERMINATOR

- SPEC:
- 1.CABLE: UL1007 28AWG
  - 2.P1 CONNECTOR: RJ45 8P8C FEMALE, GOLD PLATED
  - 3.P2 CONNECTOR: DB25P PLUG WITHOUT TERMINATOR
  - 4.25P MALE TERMINATOR GOLD PLATED
  - 5.SCREW 4-40UNC 4.5\*37MM
  - 6.POLYSHELL FRENCH BLACK IN COLOR

THIRD ANGLE PROJECTION



GENERAL NOTES

DIMENSIONS ARE IN MM - DO NOT SCALE  
 THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM



PRODUCT ID	GC258MF		
DESCRIPTION	DB25 to RJ45 Modular Adapter - M/F		
DO NOT SCALE	SHEET: 1 OF: 1	UPLOAD DATE: 8/02/2022	