





SIDE VIEW



BACK VIEW



SIDE VIEW



BACK VIEW

PIN ASSIGNMENT

TYPE A PIN	Signal Name	TYPE A PIN	WIRE
1	TMDS DATA2+	1	WHITE
2	TMDS DATA2 SHIELD	2	DRAIN
3	TMDS DATA2-	3	RED
4	TMDS DATA1+	4	WHITE
5	TMDS DATA1 SHIELD	5	DRAIN
6	TMDS DATA1-	6	BLUE
7	TMDS DATA0+	7	WHITE
8	TMDS DATA0 SHIELD	8	DRAIN
9	TMDS DATA0-	9	BROWN
10	TMDS CLOCK+	10	WHITE
11	TMDS CLOCK SHIELD	11	DRAIN
12	TMDS CLOCK-	12	GREEN
13	CEC	13	RED
14	Utility/HEAC+	14	WHITE
15	SCL	15	YELLOW
16	SDA	16	ORANGE
17	DDC/CEC GROUND	17	DRAIN
18	+5V POWER	18	WHITE
19	HOT PLUG DETECT/HEAC-	19	BLACK

ITEM	DESCRIPTIONS	QTY
③	HDMI CABLE, [(24AWG*1PAIR+DRAIN+AL+MY)*5PCS+24AWG*4 CONDUCTORS]+F+ADB,PVC JACKET,COLOR:BLACK	1
②	PVC MOLDING HOUSING,COLOR:BLACK	2
①	HDMI 19 PIN MALE CONNECTOR,METAL SHELL GOLD PLATED, INSULATOR COLOR:BLACK	2

THIRD ANGLE PROJECTION

GENERAL NOTES
 DIMENSIONS ARE IN MM - DO NOT SCALE
 THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM

StarTech.com

PRODUCT ID	HDMM7MP
DESCRIPTION	7m (22.9ft) Premium Certified High Speed HDMI Cable, 4K 60Hz/1440p 144Hz
DO NOT SCALE	SHEET: 1 OF: 1
UPLOAD DATE: 9/09/2025	