


Electrical Test:

- 1、 100% Test,short,miss wire)
- 2、 Contact Resistance: 3 ohm (MAX)
- 3、 Insulation Resistance:DC 300V/10ms,10M ohm(MIN)



10	MINI DisplayPort Male~PVC~Boarding Cap
9	DisplayPort Male~PVC~Boarding Cap
8	DisplayPort Male~32+32AWG~Clamp
7	Tube~1.5MM~Black
6	PVC~45P~Black
5	LDPE
4	DisplayPort Male~lower Shell~Black~ABS
3	DisplayPort Male~upper Shell~Black~ABS
2	DisplayPort Male~Shell Gold plated~Insulator Black~Pin Gold plated
1	MINI DisplayPort Male TO Male Cable~32+32AWG~OD:4.8mm~Nickel Plated~Black~L=6.14m~PVC+ABS Shell
NO	DESCRIPTION

THIRD ANGLE PROJECTION

GENERAL NOTES
DIMENSIONS ARE IN MM - DO NOT SCALE
THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM

PRODUCT ID	MDP2DPMM10
DESCRIPTION	10ft (3m) Mini DisplayPort to DisplayPort 1.2 Cable
DO NOT SCALE	SHEET: 1 OF: 1
	UPLOAD DATE: 4/20/2023