


Electrical Test:  
 1、100% Test, short, miss wire)  
 2、Contact Resistance: 4 ohm (MAX)  
 3、Insulation Resistance: DC 300V/10ms, 10M ohm (MIN)  
 4、Test 4K\*2K@60HZ



10	Mini DP M <sup>^</sup> Boarding Cap
9	DP M <sup>^</sup> Boarding Cap
8	DP M <sup>^</sup> ABS <sup>^</sup> lower Shell <sup>^</sup> BLACK
7	DP M <sup>^</sup> ABS <sup>^</sup> upper Shell <sup>^</sup> BLACK
6	DP M <sup>^</sup> Connector <sup>^</sup> Black insulation <sup>^</sup> shell Gold <sup>^</sup> PIN Gold
5	Mini DP M <sup>^</sup> ABS <sup>^</sup> upper Shell <sup>^</sup> BLACK
4	Mini DP M <sup>^</sup> ABS <sup>^</sup> lower Shell <sup>^</sup> BLACK
3	Mini DP M <sup>^</sup> Connector <sup>^</sup> White insulation <sup>^</sup> shell Gold <sup>^</sup> PIN Gold
2	PVC <sup>^</sup> 45P <sup>^</sup> BLACK
1	DP1. 4 <sup>^</sup> [32AWG (7/0. 08TC)+EAM]*5P+32AWG (7/0. 08TC)*4C+AEB (16/7/0. 12AL 85%) <sup>^</sup> OD:4. 8MM <sup>^</sup> BLACK <sup>^</sup> PVC <sup>^</sup> UL printing
NO	DESCRIPTION

THIRD ANGLE PROJECTION

**StarTech.com**

<b>GENERAL NOTES</b>		PRODUCT ID		MDP2DPMM10	
DIMENSIONS ARE IN MM - DO NOT SCALE		DESCRIPTION		10ft (3m) Mini DisplayPort to DisplayPort 1.2 Cable	
THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM		<b>DO NOT SCALE</b>		<b>SHEET: 1 OF: 1</b>	
				<b>UPLOAD DATE: 9/03/2025</b>	