


Note:
1.Support Resolution:3840*2160/30Hz.

MDP2HDMM1MB	1000±10mm
MDP2HDMM2MB	2000±20mm
MDP2HDMM3MB	3000±30mm
PART NO	Length(L±M)

4	60P PVC,Color Black
3	LDPE (RoHs)-PE101
2	HDMI A/M Black Front Cover
	HDMI A/M Black Case
	PCBA/DP TO HDMI A/M \IC:PS8402\Conn nickel plating
1	Mini DP(Housing) to DP(Housing)Cable(nickel plating) UL20276(32AWG*1P+D+AL/MY)*5C+32AWG*5C+D+AL+BRAID,JACKET PVC BLACK.OD=5.5mm
NO	DESCRIPTION

THIRD ANGLE PROJECTION



GENERAL NOTES

DIMENSIONS ARE IN MM - DO NOT SCALE
THIS DOCUMENT CONTAINS CONFIDENTIAL,
PROPRIETARY INFORMATION THAT IS
PROPERTY OF STARTECH.COM

StarTech.com

PRODUCT ID	MDP2HDMMxMB
DESCRIPTION	Mini DisplayPort to HDMI Adapter Cable - 4K 30Hz
DO NOT SCALE	SHEET: 1 OF: 1
	UPLOAD DATE: 5/12/2026