


**PINOUT:**

P1	CONDUCTOR	P2
1	PURPLE	1
2	RED	2
3	PINK	3
4	LIGHT GREEN	4
5	BROWN/WHITE	5
6	WHITE	6
7	GREEN	7
8	YELLOW	8
10	BLUE	10
11	BROWN	11
12	ORANGE	12
13	GRAY	13
14	BLACK	14
15	LIGHT BLUE	15
SHELL	DRAIN	SHELL

- SPEC:**
- CABLE NON-UL 14CONDUCTOR 28AWG 100%AL DRAIN  
JACKET GRAY IN COLOR OD:5.3mm
  - CONNECTOR HDD15PIN MALE PIN9 REMOVED SHELL NICKEL PLATED
  - 100% METAL SHELL OF HDD15PIN CONNECTORS
  - MOLDING SCREW 4-40UNC 4x38.5MM
  - MOLDING PVC GRAY IN COLOR.

**THIRD ANGLE PROJECTION**



**GENERAL NOTES**

DIMENSIONS ARE IN MM - DO NOT SCALE  
THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM



PRODUCT ID	MXT101MM
DESCRIPTION	6 ft Monitor VGA Cable - HD15 M/M
<b>DO NOT SCALE</b>	<b>SHEET: 1 OF: 1</b>
	<b>UPLOAD DATE: 2/22/2022</b>