




8 7 6 5 4 3 2 1



THIRD ANGLE PROJECTION



**StarTech.com**

**GENERAL NOTES**

DIMENSIONS ARE IN MM - DO NOT SCALE  
THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM

PRODUCT ID	PXT1011410		
DESCRIPTION	10 ft 14 AWG Computer Power Cord - NEMA5-15P to C13		
<b>DO NOT SCALE</b>	<b>SHEET: 1 OF: 1</b>	<b>UPLOAD DATE: 10/27/2021</b>	

Conductor		Insulation			Jacket		Overall diameter
AWG	Resistance maximum	Min.Thick	Diameter	Length of Lay	Min.Thick	AVG.Thick	
14# (41/0.246)	at 20°C ≤ 8.88ohm/km at 25°C ≤ 9.06ohm/km	0.69mm	3.5±0.1mm	83↓mm	0.61mm	0.76mm	9.25±0.1mm

8 7 6 5 4 3 2 1