



Polarity and Conduction and Puncture Test	
Dielectric Voltage Withstand Test : 1500V / 1 Sec	
Electrical Performance (20°C)	
Item	Parameter
Conductor Resistance	≤ 22.84Ω/1000m
Voltage Rating	AC 300V

Product No.	Length
PXT101L3	914±15
PXT101L	1830±20
PXT101L10	3050±30

PINOUT			
SF-31		SF-83	WIRE
E		E	GREEN
L		L	BLACK
N		N	WHITE

⑦	Molding	Molding 40P PVC Black
⑥	Housing	SF-83 One piece of inner frame Three plug, Black ABS
⑤	Housing	SF-31 One piece of inner frame Three plug, Black ABS
④	Terminal	IEC C13 Three plug Female Straight insert of Common terminal, brassy yellow, 18AWG
③	Terminal	5-15P Three plug Male Straight insert of Current-carrying terminal, Nickel plated, 18AWG
②	Terminal	5-15P Three Plug Male Straight insert of Grounding terminal, Nickel plated, 18AWG
①	Cable	SVT 18AWG 3C 60° Black PVC
No.	TITLE	DESCRIPTION

THIRD ANGLE PROJECTION

GENERAL NOTES
DIMENSIONS ARE IN MM - DO NOT SCALE

THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM

StarTech.com

PRODUCT ID	PXT101Lxx	
DESCRIPTION	Computer Power Cord, 5-15P to Right Angle C13 Cable	
DO NOT SCALE	SHEET: 1 OF: 1	UPLOAD DATE: 4/23/2025