



Customer Item NO.	Cable Color	Molding Color	Length
PXT101	Black	Black	1830±20
PXT10115	Black	Black	4572±30
PXT101_10	Black	Black	3050±30
PXT10112	Black	Black	3660±30

PINOUT			
SF-31		SF-82S	WIRE
E		E	GREEN
L		L	BLACK
N		N	WHITE

Polarity and Conduction and Puncture Test	
Dielectric Voltage Withstand Test : 1500V / 1 Sec	
Electrical Performance (20°C)	
Item	Parameter
Conductor Resistance	≤ 22.4Ω/1000m
Voltage Rating	AC 300V

⑥	Molding	Molding 40P PVC Black	40G
⑤	Housing	SF-82S One piece of inner frame brassy yellow Three plug,Black ABS	1PC
④	Housing	SF-31 One piece of inner frame,5-15P,Three plug,Black ABS	1PC
③	Terminal	5-15P Three Plug Male Straight insert Grounding of terminal,Brass Nickel plated,18AWG	1PC
②	Terminal	5-15P Three plug Male Straight insert Current-carrying of terminal,Brass Nickel plated,18AWG	2PCS
①	Cable	SVT 18AWGX3C 60°C Black PVC	1PC

THIRD ANGLE PROJECTION

GENERAL NOTES
 DIMENSIONS ARE IN MM - DO NOT SCALE
 THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM

StarTech.com

PRODUCT ID	PXT101x
DESCRIPTION	6 ft Standard Computer Power Cord - NEMA5-15P to C13
DO NOT SCALE	SHEET: 1 OF: 1
	UPLOAD DATE: 2/15/2022

No.	TITLE	DESCRIPTION	Q'TY
8			
7			
6			
5			
4			
3			
2			
1			