


WIRE MARKING: (UL) E135710-F3 SVT 3X18AWG 60°C 300V VW-1 CSA LL95737 SVT 3X0.824mm<sup>2</sup>(18AWG) 60°C 300V FT2 YFC-BONEAGLE

REMARKS:

1. PLUG(SF-33) RATED POWER:125V 10A
2. CONNECTOR(SF-82) RATED POWER:125V 10A
3. WIRE:SVT 3X18AWG 60°C RATED VOLTAGE:300V
4. DVW TEST:1500VAC,1S
5. POLARIZATION AND CONTINUITY TEST
6. COLOR:BLACK
7. COMPLY WITH UL817 STANDARD

SKU	LENGTH(FT)
PXTMG1011	1FT±0.1FT
PXTMG1013	3FT±0.1FT
PXTMG1016	6FT±0.13FT
PXTMG10110	10FT±0.16FT
PXTMG10115	15FT±0.16FT

THIRD ANGLE PROJECTION



GENERAL NOTES

DIMENSIONS ARE IN MM - DO NOT SCALE

THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM

StarTech.com

PRODUCT ID	PXTMG101xx		
DESCRIPTION	18AWG, NEMA 5-15P to C13, 10A 125V, Green Dot Medical Power Cable		
DO NOT SCALE	SHEET: 1 OF: 1	UPLOAD DATE: 12/02/2022	