



Wire Pin Assignment and Wire Description:

CN.1	Signal Name	CN.2	COLOR
A4,B4,A9,B9	PWR_Vbus1	A4,B4,A9,B9	RED
A5	CC	A5	BLUE
A7	UTP_Dn	A7	WHITE
A6	UTP_Dp	A6	GREEN
A1,B1,A12,B12	GND_PWRrt1	A1,B1,A12,B12	DRAIN
SHORT SHELL		SHORT SHELL	BRAID

Part NO.	Length(mm)
R2CCR-15C-USB-CABLE	(6inch)152±20
R2CCR-30C-USB-CABLE	300±30
R2CCR-1M-USB-CABLE	1000±30
R2CCR-2M-USB-CABLE	2000±30

MOLDED TPE COLOR(PT 123C)	4
MOLDED TPE COLOR(BLACK)	3
USB 2.0 TYPE C MALE, TERMINAL Au-Plated, SHELL Ni-Plated	2
USB 2.0 [32AWGx2C+22AWGx1C+32AWGx1C+2E]+AB OD:3.1mm JACKET TPE BLACK	1
<b>MATERIALS LIST &amp; SPEC. DESCRIPTION</b>	<b>ITEM</b>

THIRD ANGLE PROJECTION

**GENERAL NOTES**  
DIMENSIONS ARE IN MM - DO NOT SCALE

THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM

**StarTech.com**

PRODUCT ID	R2CCR-xM-USB-CABLE
DESCRIPTION	Heavy Duty Right Angle Fast Charge USB-C Cable - 60W PD 3A
<b>DO NOT SCALE</b>	<b>SHEET: 1 OF: 1</b>
	<b>UPLOAD DATE: 2/14/2023</b>