


⑧	Outside mold~Black
⑦	Outside mold~Yellow
⑥	2.5*39.2-M2*0.4~2.5*39.2-M2*0.4~Fe~Plating Nickel
⑤	USB TYPE C SOLDER TYPE TIN Plating Nickel Left
④	USB TYPE C SOLDER TYPE TIN Plating Nickel Right
③	TYPE-C-USB C Type Connector With~PCB+SMT
②	TYPE-C-USB C Type Connector With~PCB+IC+SMT
①	23AWG (55/0.08TC)*2C+30AWG (19/0.06TC)*2C+30AWG (26/0.05TC)*2C+4E (68/0.08TC) ~OD:4.2MM +Braided-OD:4.7MM

NO	ITEM	DESCRIPTION
8		
7		
6		
5		

THIRD ANGLE PROJECTION



GENERAL NOTES

DIMENSIONS ARE IN MM - DO NOT SCALE
 THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM



PRODUCT ID	S2CEPR2M-USBSL-CABLE
DESCRIPTION	6ft (2m) USB-C Charging Cable, Durable and Ultra-Flexible, Side Screw Locking, 240W (5A) PD EPR, USB 2.0
DO NOT SCALE	SHEET: 1 OF: 1
	UPLOAD DATE: 10/31/2025

8	7	6	5	4	3	2	1
---	---	---	---	---	---	---	---