



⑧	Outside mold~Black
⑦	Outside mold~Yellow
⑥	2.5*39.2-M2*0.4~2.5*39.2-M2*0.4~Fe~Plating Nickel
⑤	USB TYPE C SOLDER TYPE TIN Plating Nickel Left
④	USB TYPE C SOLDER TYPE TIN Plating Nickel Right
③	TYPEC-USB C Type Connector With~PCB+SMT
②	TYPEC-USB C Type Connector With~PCB+IC+SMT
①	28AWG (19/0.08TC)*2C+21AWG (80/0.08TC+250D Nylon)*2C+30AWG (26/0.05TC)*2C+3E (110/0.08TC+250D Nylon)+E (65/0.08TC)~OD:4.7MM~Braided~OD:5.2MM
NO	DESCRIPTION

THIRD ANGLE PROJECTION

GENERAL NOTES
DIMENSIONS ARE IN MM - DO NOT SCALE

THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM

StarTech.com

PRODUCT ID	S2CEPR3M-USBSL-CABLE
DESCRIPTION	10ft (3m) USB-C Charging Cable, Durable and Ultra-Flexible, Side Screw Locking, 240W (5A) PD EPR
DO NOT SCALE	SHEET: 1 OF: 1
UPLOAD DATE: 5/14/2026	