



P3



TOLERANCE: $\pm 0.5\text{mm}$




850 $\pm 25\text{mm}$


300 $\pm 15\text{mm}$

300 $\pm 15\text{mm}$

1500 $\pm 40\text{mm}$





P1




P2

P4




P2



P1

ITEM.	DESCRIPTIONS	Q'TY
P4	PUSH BUTTON	1PCS
P3	2-PORT HDMI KVM SWITCH	1PCS
P2	USB AM MD TYPE/C:BLACK	2PCS
P1	VGA PLUG MD TYPE/C:BLACK	2PCS

THIRD ANGLE PROJECTION



GENERAL NOTES

DIMENSIONS ARE IN MM - DO NOT SCALE
THIS DOCUMENT CONTAINS CONFIDENTIAL,
PROPRIETARY INFORMATION THAT IS
PROPERTY OF STARTECH.COM

StarTech.com

PRODUCT ID	SV211USB		
DESCRIPTION	2 Port USB VGA Cable KVM Switch - USB Powered with Remote		
DO NOT SCALE	SHEET: 1 OF: 1	UPLOAD DATE: 2/10/2023	