



NO	DESCRIPTION	Q'TY	UNIT
8	Insulating tape~W=5MM	0.024	m
7	Copper foil~W=5MM 25u	0.024	m
6	USB TYPE C~lower mater cover~Nickel Plated	2	pcs
5	USB TYPE C~upper mater cover~Nickel Plated	2	pcs
4	PVC~45P~Black	16	g
3	Low pressure molding material	2	g
2	C Type Connector With~PCB+SMT~Shell Nickel Plated	2	pcs
1	[30AWG(19/0.06TC)*1P+AL]+22#(41/0.10TC+250D)*1C+30AWG(7/0.10TC)*1C+3E(26/0.10+250D)+AB(16/9/0.06TC 85%TC)~OD:3.8~Black~PVC	0.52	m

THIRD ANGLE PROJECTION

GENERAL NOTES
 DIMENSIONS ARE IN MM - DO NOT SCALE
 THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM

StarTech.com

PRODUCT ID	USB2CC50CM
DESCRIPTION	USB-C Cable - M/M - 0.5 m - USB 2.0
DO NOT SCALE	SHEET: 1 OF: 1
	UPLOAD DATE: 12/08/2021