






10FT (3050 ± 30mm)



USB "A" M




①



USB "B" M




PINOUT



CABLE:UL2725 28#*1P+22#*2C+1+AL+B OD4.8 BLACK PVC JACKET
 CONNECTOR:USB A TYPE4PIN MALE NICKELPLATED
 CONNECTOR:USB B TYPE MALE NICKEL PLATED
 MOLDING TYPE
 CONDUCTING RESISTANCE:5 Ω
 INSULATION RESISTANCE:5 Ω

THIRD ANGLE PROJECTION



GENERAL NOTES

DIMENSIONS ARE IN MM - DO NOT SCALE
 THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM

StarTech.com

PRODUCT ID	USB2HAB10		
DESCRIPTION	10 ft USB 2.0 Certified A to B Cable - M/M		
DO NOT SCALE	SHEET: 1 OF: 1	UPLOAD DATE: 3/20/2026	