


8	High temperature adhesive paper
7	Copper foil
6	Black heat shrinkage casing
5	60P PVC BLACK
4	LDPE; Rolls
3	PCBA USB3.0 TO ESATA; Black rubber core\Connector nickel plating; IC:ASM1153E
2	ESATA(Molding) to ESATA(Molding)Cable\Connector nickel plating. (1/0. 40T*2C+AL)*2P+4D+MY+AL+B(16/9/0. 12TC), JACKET PVC BLACK OD:5. 5mmmm
1	USB3. 0 A\M(Molding) to USB3. 0 A\M(Molding) Cable\Connector nickel plating. (7/0. 127T*1P+D+AL+MYLAR)*2C+7/0. 127T*1P+7/0. 127T*2C+F+AB(16/6/0. 1T), JACKET PVC Black OD=5. 5mm
NO	DESCRIPTION

THIRD ANGLE PROJECTION

StarTech.com

GENERAL NOTES

DIMENSIONS ARE IN MM - DO NOT SCALE

THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM

PRODUCT ID	USB3S2ESATA3		
DESCRIPTION	USB 3.0 to eSATA HDD / SSD / ODD Adapter Cable		
DO NOT SCALE	SHEET: 1 OF: 1	UPLOAD DATE: 3/29/2023	