


**PIN ASSIGNMENT:**

AM	Pin Signal Name		AM	Pin Signal Name
1	VBUS		1	VBUS
2	D-		2	D-
3	D+		3	D+
4	GND		4	GND
5	SSRX-		8	SSTX-
6	SSRX+		9	SSTX+
7	GND_Drain		7	GND_Drain
8	SSTX-		5	SSRX-
9	SSTX+		6	SSRX+
Shell	Shield		Shell	Shield

- NOTES:**
1. ALL MATERIAL MEET THE ROHS2.0 COMPLIANT
  2. 100% OPEN/SHORT/MISS WIRE TESTING
  3. INSULATION RESISTANCE: DC/250V, 10MΩ MIN, 0.01S
  4. WITHSTAND VOLTAGE: AC/250V 5mA FOR 0.1S.
  5. CONDUCTOR RESISTANCE: 5Ω MAX.

④	PVC	OVER MOLDING : 30P BLACK	A/R
③	PE	IN MOLDING : MG70 LDPE	A/R
②	USB3.0 AM	USB3.0 A/M, Contact:G/F, Blue Insulation, Nickel Plated Shell.	2 SET
①	Cable	USB 3.0 CABLE 28AWG*[1P(7/0.127TC)+D.W(7/0.127TC)]*2+28AWG*1P(7/0.127TC)+24AWG(7/0.196TC) *2C+AL-MYLAR+BRAID (Al-Mg) , Black PVC Jacket, OD:5.5±0.2mm	A/R
No.	TITLE	DESCRIPTION	Q' TY

THIRD ANGLE PROJECTION



**GENERAL NOTES**

DIMENSIONS ARE IN MM - DO NOT SCALE  
THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM



PRODUCT ID	USB3SAA3MBK
DESCRIPTION	USB 3.0 (5Gbps) Cable - A to A - M/M - 3 m (10 ft.)
<b>DO NOT SCALE</b>	<b>SHEET: 1 OF: 1</b>
	<b>UPLOAD DATE: 5/06/2026</b>