

P1


A1,B1,A12,B12	GND	GND
A4,B4,A9,B9	RED	VBUS
(CC) A5		5.1K Pull down
(VCONN2) B5		NC
(Dp1) A6	GREEN	D+
(Dn1) A7	WHITE	D-
(TXp1) A2	YELLOW	TX1+
(TXn1) A3	BLUE	TX1-
(RXp1) B11	ORANGE	RX1+
(RXn1) B10	PURPLE	RX1-
(TXp2) B2		NC
(TXn2) B3		NC
(RXp2) A11		NC
(RXn2) A10		NC
(RFU1) A8		NC
(RFU2) B8		NC

P2

1	VBUS
2	D-
3	D+
4	GND
5	SSRX-
6	SSRX+
7	GND
8	SSTX-
9	SSTX+

- 1:UL30AWG/2P+32AWG/1P+24AWG/2C+F+ADB, OD4.5mm, PVC outer cover, Black
- 2:External mold: PVC 45P Black
- 3:Internal mold: LDPE Colourless
- 4:SR: PVC 45P Black
- 5:Enclosure: ABS Black

THIRD ANGLE PROJECTION



GENERAL NOTES

DIMENSIONS ARE IN MM - DO NOT SCALE
 THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM



PRODUCT ID	USBC3LINK		
DESCRIPTION	USB-C to USB Data Transfer Cable for Mac and Windows - USB 3.0		
DO NOT SCALE	SHEET: 1 OF: 1	UPLOAD DATE: 12/20/2024	