

## 2 Port Auto High Speed HDMI Switch

VS122HDMIU

DE: Bedienungsanleitung - de.startech.com

FR: Guide de l'utilisateur - fr.startech.com

ES: Guía del usuario - es.startech.com

IT: Guida per l'uso - it.startech.com

NL: Gebruiksaanwijzing - nl.startech.com

PT: Guia do usuário - pt.startech.com

### Packaging Contents

- 1 x VS122HDMIU switch
- 1 x HDMI cable

### System Requirements


- HDMI enabled display device (i.e. HDTV, monitor, projector, etc.)
- HDMI enabled video sources (i.e. computer, game console, etc.)

### Installation

1. Connect an HDMI cable (not included) from each of the video source devices (i.e. computer, game console, DVR, etc.) to the 'IN' connectors on the video switch. Port 1 is the primary input so will be displayed by default.
2. Connect an HDMI cable from the display device (i.e. HDTV, monitor, etc.) to the 'OUT' connector on the video switch.
3. Turn on the display device, followed by the video sources.

If the video signal on Port 1 is terminated (i.e. turned off, cable disconnected, etc.), then the video switch will automatically select Port 2. Once the video signal is restored on Port 1, the video switch will automatically switch back to Port 1.

The video switch can be manually toggled between ports by pressing the "Select" button on the top of the unit. This setting will remain until the video signal on Port 1 changes, setting it back to automatic mode.



### Specifications

<b>Video Signal</b>	HDMI (1.3)
<b>Number of Ports</b>	2
<b>Connectors</b>	3 x HDMI type A female
<b>LEDs</b>	1 x Power 2 x Port Selection Indicator
<b>Video Bandwidth</b>	2.5Gbps
<b>Maximum Video Resolution</b>	1080p
<b>Maximum Cable Distance</b>	10 m
<b>Audio Support</b>	Yes
<b>HDCP Compliant</b>	Yes (HDCP 1.1)
<b>Power Adapter</b>	Self-powered
<b>Operating Temperature</b>	0°C ~ 70°C (32°F ~ 158°F)
<b>Storage Temperature</b>	-65°C ~ 150°C (-85°F ~ 302°F)
<b>Humidity</b>	10% ~ 85% RH
<b>Dimensions</b>	63.0mm x 59.0mm x 15.0mm
<b>Weight</b>	35g

## FCC Compliance Statement

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

## Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. Regardless of any direct acknowledgement elsewhere in the body of this document, StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

## Technical Support

StarTech.com's lifetime technical support is an integral part of our commitment to provide industry-leading solutions. If you ever need help with your product, visit [www.startech.com/support](http://www.startech.com/support) and access our comprehensive selection of online tools, documentation, and downloads.

For the latest drivers/software, please visit [www.startech.com/downloads](http://www.startech.com/downloads)

## Warranty Information

This product is backed by a two year warranty.

In addition, StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

## Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.