

Deep Fixed Server Rack Cabinet Shelf for the 7236CABINET

CABSHELFD

DE: Bedienungsanleitung - de.startech.com

FR: Guide de l'utilisateur - fr.startech.com

ES: Guía del usuario - es.startech.com

IT: Guida per l'uso - it.startech.com

NL: Gebruiksaanwijzing - nl.startech.com

PT: Guia do usuário - pt.startech.com



*actual product may vary from photos

Packaging Contents

- 1 x Fixed Shelf
- 4 x M5 Nut
- 4 x M5 Cabinet Screw
- 4 x M5 Washer
- 2 x Mounting Bracket

System Requirements

- EIA-310C compliant 19in server rack/cabinet
- At least 1U of available space in rack/cabinet to mount shelf
- If using a rack/cabinet that does not use square mounting points along the posts, the appropriate mounting hardware for the rack will be required (consult documentation for the rack or contact the manufacturer)

Installation



Deep Shelf - Before installing the deep shelf into the cabinet you must first join the mounting bracket to the shelf using the screws and nuts provided. Move the nuts in the cabinet to the desired height and fasten the shelves brackets to the front and rear posts.

Specifications

Description	Deep Fixed Server Rack Cabinet Shelf
Material	SPCC (1.6mm thick)
Color	Black
Maximum Weight Capacity	75kg
Mounting Height	1U
External Dimensions (WxDxH)	466mm x 690mm x 38mm
Net Weight	8.8kg
Certifications	RoHS

Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. Regardless of any direct acknowledgement elsewhere in the body of this document, StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

Technical Support

StarTech.com's lifetime technical support is an integral part of our commitment to provide industry-leading solutions. If you ever need help with your product, visit www.startech.com/support and access our comprehensive selection of online tools, documentation, and downloads.

For the latest drivers/software, please visit www.startech.com/downloads

Warranty Information

This product is backed by a lifetime warranty.

In addition, StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.