






CONNECTION


DP PLUG	PAIR#	PIN NAME	COLOR	DP PLUG
1	PAIR1 BLUE	ML_Lane 0(p)	BLUE	12
2		GND	DRAIN	11
3		ML_Lane 0(n)	WHITE	10
4	PAIR2 BROWN	ML_Lane 1(p)	BLUE	9
5		GND	DRAIN	8
6		ML_Lane 1(n)	WHITE	7
7	PAIR3 RED	ML_Lane 2(p)	BLUE	6
8		GND	DRAIN	5
9		ML_Lane 2(n)	WHITE	4
10	PAIR4 YELLOW	ML_Lane 3(p)	BLUE	3
11		GND	DRAIN	2
12		ML_Lane 3(n)	WHITE	1
13		CONFIG 1	ORANGE	13
14		CONFIG 2	RED	14
15	PAIR5 GREEN	AUX_CH(p)	BLUE	15
16		GND	DRAIN	16
17		AUX_CH(n)	WHITE	17
18		Hot plug Detect	BROWN	18
19		GND	YELLOW	19
SHELL	GND	Braid(GND)	GND	SHELL

ELECTRIC TESTING:
1.100% OPEN & SHORT TESTING
2.INSULATION RESISTANCE: $\geq 20M\Omega$
3.CONDUCTOR RESISTANCE: $\leq 3\Omega$
4.VOLTAGE: 300V DC/0.1S

PRODUCT SKU	LENGTH(mm)	COLOUR	TOLERANCE(mm)
DISPLPORT15L	4570	BLACK	± 150
DISPL5M	5000	BLACK	± 200

ITEM	DESCRIPTIONS	Q'TY
⑧	PVC MOLDING STRAIN RELIEF,COLOR:BLACK	2
⑦	LD PE MOLDING INTERNAL MODEL,COLOR:CLEAR	2
⑥	METAL BOTTOM SHELL, USED FOR DP CONNECTOR	2
⑤	METAL TOP SHELL, USED FOR DP CONNECTOR	2
④	ABS BOTTOM SHELL,USED FOR DP CONNECTOR,COLOR:BLACK	2
③	ABS TOP SHELL,USED FOR DP CONNECTOR,COLOR:BLACK	2
②	DP 20P MALE CONNNECTOR,TERMINALS GOLD PLATED,METAL SHELL NI PLATED, INSULATOR COLOR:BLACK	2
①	DP CABLE,(26AWG*1P+AEM)*5+28AWG*4C+F+AEB,PVC JACKET,COLOR:BLACK	1

THIRD ANGLE PROJECTION



GENERAL NOTES

DIMENSIONS ARE IN MM - DO NOT SCALE
THIS DOCUMENT CONTAINS CONFIDENTIAL,
PROPRIETARY INFORMATION THAT IS
PROPERTY OF STARTECH.COM

StarTech.com

PRODUCT ID	DISPL5M, DISPLPORT15L		
DESCRIPTION	DisplayPort 1.2 Cable - 4K x 2K Ultra HD VESA Certified Latching Connectors		
DO NOT SCALE	SHEET: 1 OF: 1	UPLOAD DATE: 11/24/2021	