



PINOUT:




PINOUT:



SPEC:

- CABLE UL2919 28AWG/3COAX+28AWG*3P+28AWG*2C+ADB
JACKET BLACK IN COLOR OD:8.6MM(Conductor Resistance: AT 20°C MAX 237.25Ω/km.
Insulation Resistance: 10MΩ-km min AT 20°C DC 500V)
- CONNECTOR HDD15P FEMALE BLACK COLOR PIN&SHELL GOLD PLATED
- CONNECTOR LFH60P MALE BLACK COLOR PIN&SHELL GOLD PLATED
- MLODING SCREW 4-40UNC 4*45MM
- NUT 4-40UNC 4.75*8.1MM
- 100%METAL SHELL OF HDD15P&LFH CONNECTORS
- MOLDING PVC BLACK IN COLOR

THIRD ANGLE PROJECTION



GENERAL NOTES

DIMENSIONS ARE IN MM - DO NOT SCALE
THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM



PRODUCT ID	DMSVGA1		
DESCRIPTION	8in LFH 59 Male to Dual Female VGA DMS 59 Cable		
REV: A	DO NOT SCALE	SHEET : 1 OF: 1	DATE: 06/15/2020