


WIRE LIST

| P1 | PAIR# | COLOR | P2 |
|-------|--------|-------|-------|
| 1 | PAIR1 | RED | 2 |
| 2 | | DRAIN | 3 |
| 3 | | WHT | 1 |
| 4 | PAIR2 | GRN | 10 |
| 5 | | DRAIN | 11 |
| 6 | PAIR3 | WHT | 9 |
| 7 | | BLUE | 18 |
| 8 | | DRAIN | 19 |
| 9 | PAIR4 | WHT | 17 |
| 10 | | BRN | 23 |
| 11 | PAIR4 | DRAIN | 22 |
| 12 | | WHT | 24 |
| 13 | | N/A | |
| 14 | | N/A | |
| 15 | SIGNAL | VIO | 6 |
| 16 | SIGNAL | BRN | 7 |
| 17 | GND | ORN | 15 |
| 18 | SIGNAL | YEL | 14 |
| 19 | SIGNAL | WHT | 16 |
| SHELL | | BRAID | SHELL |

THIRD ANGLE PROJECTION



GENERAL NOTES

DIMENSIONS ARE IN MM - DO NOT SCALE
 THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM

StarTech.com

| | |
|---------------------|--|
| PRODUCT ID | DP2DVIMM10 |
| DESCRIPTION | 10 ft DisplayPort to DVI Video Adapter Converter Cable - M/M |
| DO NOT SCALE | SHEET: 1 OF: 1 |
| | UPLOAD DATE: 9/23/2021 |