



Wire Pin Assignment and Wire Description:

CN. 1	PAIR#	CN. 2	COLOUR
2	✕	1	WHITE
1		3	ORANGE
3	PAIR1	2	DRAIN
10	✕	4	RED
9		6	WHITE
11	PAIR2	5	DRAIN
18	✕	7	GREEN
17		9	WHITE
19	PAIR3	8	DRAIN
23	✕	10	BLUE
24		12	WHITE
22	PAIR4	11	DRAIN
6	SIGNAL	15	GREEN
7	SIGNAL	16	YELLOW
15	SIGNAL	17	PURPLE
14	SIGNAL	18	RED
16	SIGNAL	19	BLUE
SHELL		SHELL	BRAID

Length table:

Part NO.(F)	Length(L)
HDMIDVIMM20	6090±100
HDDVIMM25	7620±100
HDMIDVIMM30	9100±100
HDMIDVIMM50	15240±150
HDDVIMM7M	7000±100
HDDVIMM10M	10000±100
HDDVIMM15M	15000±150

⑤	DVI Thumb 4-40 UNC Screws BLACK	2PCS
④	MOLDING:PVC BLACK	/
③	DVI 18+1 MALE (GOLD PLATED CONTACTS,GOLD PLATED SHELL.)	1
②	HDMI A MALE 19 PIN. (GOLD PLATED CONTACTS,GOLD PLATED SHELL.)	1
①	HDMI CABLE: [(24AWG*2C+EAM)*4P+(28AWG*2C+EMA)+(28AWG*4C)]+AB, OD:10.0mm Bare Copper:85% Jacket Color: Black PVC	/
ITEM	MATERIALS LIST & SPEC. DESCRIPTION	Q'TY

THIRD ANGLE PROJECTION

GENERAL NOTES
 DIMENSIONS ARE IN MM - DO NOT SCALE
 THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM

StarTech.com

PRODUCT ID	HDMIDVIMMxx
DESCRIPTION	HDMI to DVI-D Cable - M/M
DO NOT SCALE	SHEET: 1 OF: 1
UPLOAD DATE: 9/03/2021	