


PIN Assignment

P2	P1	P3
1 ——— YL ———	1	
1 ——— YL ———	2	
	3 ——— YL ———	1
2 ——— BK ———	4	
3 ——— BK ———	5	
	6 ——— BK ———	2
	7 ——— BK ———	3
	8 ——— BK ———	3

ELECTRICAL TESTING:
 (1)100% open short &miss wire test.
 (2)Insulation Resistance:≥5MΩ.
 (3)Contact Resistance:≤5Ω.
 (4)Dielectric Strength:DC 200V/0.1s.

③	CONNECTOR	4P LARGE MOLEX RECEPTACLE,BRASS TIN PLATED,SEMI-TRANSPARENT NYLON	PCS	2
②	CONNECTOR	2*4P PCI EXPRESS POWER PLUG,BRASS TIN PLATED FEMALE TERMINATOR, BLACK NYLON	PCS	1
①	CABLE	18AWG,41C*0.16TC,BLACK JACKET,PVC,OD 2.0mm	PCS	5
		18AWG,41C*0.16TC,YELLOW JACKET,PVC,OD 2.0mm	PCS	3
ITEM	P/N	DESCRIPTION	UNIT	QTY

THIRD ANGLE PROJECTION



GENERAL NOTES

DIMENSIONS ARE IN MM - DO NOT SCALE
 THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM



PRODUCT ID	LP4PCIEX8ADP		
DESCRIPTION	6in LP4 to 8 Pin PCI Express Video Card Power Cable Adapter		
REV: A	DO NOT SCALE	SHEET : 1 OF: 1	DATE: 05/13/2020