


Pin Assignment



Electrical Test:  
 1.100%Test(Open ,short ,miss wire)  
 2.Contact Resistance: 3 ohm max.  
 3.Insulation Resistance: 10M ohm Min.300V DC/10ms.

9	Mini DP TO PCB~34AWG~Clamp	1	pcs
8	Mini DP M~ABS Shell~Black	1	pcs
7	#4-40UNC H4.75*8.6MM~Nickel Plated~clinch	2	pcs
6	Mini DP M~Boarding Cap	1	pcs
5	VGA F~ABS Cover plate~Black	1	pcs
4	VGA F~ABS Shell~BlackMarking:STAR...	1	pcs
3	65P PVC Black	4	g
2	MDPV12-15CM~PCB~SMT~soldertar	1	pcs
1	MINI DP M TO MINI DP M~34AWG~OD:0.42M~Nickel Plated~Black~L=0.43m	1/2	pcs
NO	DESCRIPTION	Q'TY	UNIT

THIRD ANGLE PROJECTION

**GENERAL NOTES**  
 DIMENSIONS ARE IN MM - DO NOT SCALE  
 THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM

PRODUCT ID	MDP2VGA2
DESCRIPTION	Mini DisplayPort 1.2 to VGA Adapter Converter – 1920x1200
<b>DO NOT SCALE</b>	<b>SHEET: 1 OF: 1</b>
<b>UPLOAD DATE: 12/23/2020</b>	