


P1	COLOR	P2
4	BROWN	4
11	BROWN/WHITE	11
12	RED	12
15	RED/WHITE	15
5	ORANGE	5
5	ORANGE/WHITE	5
13	YELLOW	13
10	YELLOW/WHITE	10
14	BLACK	14
10	BLACK/WHITE	10
SHIELD		SHIELD

PINOUT:

- | | | | | |
|----|----------------------|-----|----|---|
| P1 | 1 — RED COAX COND | — 1 | P2 | 1 |
| | 2 — GREEN COAX COND | — 2 | | 2 |
| | 3 — BLUE COAX COND | — 3 | | 3 |
| | 6 — RED COAX DRAIN | — 6 | | 6 |
| | 7 — GREEN COAX DRAIN | — 7 | | 7 |
| | 8 — BLUE COAX DRAIN | — 8 | | 8 |

- SPEC:
- CABLE UL2919 3COAX+5PAIR(28AWG) 100%AL DRAIN BRAID JACKET BLACK IN COLOR
 - CONNECTOR BLACK HDD15PIN MALE PIN9 REMOVED PIN GOLD PLATED
 - MOLDING SCREW 4-40UNC 4x49.5mm.
 - FERRITE CORE 17.5*28.5*10.5MM
 - 100%METAL SHELL OF HDD15PIN CONNECTORS
 - MOLDING PVC BLACK IN COLOR.

THIRD ANGLE PROJECTION



GENERAL NOTES

DIMENSIONS ARE IN MM - DO NOT SCALE
 THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM



PRODUCT ID	MXT105MMHQ
DESCRIPTION	15 ft Coax High Resolution Monitor VGA Cable - HD15 M/M
DO NOT SCALE	SHEET: 1 OF: 1
	UPLOAD DATE: 2/1/2021