


8 7 6 5 4 3 2 1

LENGTH(xx)



PART NUMBER	COLOR	LENGTH(xx)
MXTMMHQ50CM	BLACK	500+20/-0mm
MXTMMHQ1M	BLACK	1000+20/-0mm
MXTMMHQ2M	BLACK	2000+30/-0mm
MXTMMHQ3M	BLACK	3000+30/-0mm
MXTMMHQ5M	BLACK	5000+40/-0mm
MXTMMHQ7M	BLACK	7000+40/-0mm
MXTMMHQ10M	BLACK	10000+80/-0mm
MXTMMHQ15M	BLACK	15000+80/-0mm
MXTMMHQ20M	BLACK	20000+100/-0mm
MXTMMHQ25M	BLACK	25000+100/-0mm
MXTMMHQ30M	BLACK	30000+100/-0mm


PINOUT:

P1		P2
1	— RED COAX COND —	1
2	— GREEN COAX COND —	2
3	— BLUE COAX COND —	3
6	— RED COAX DRAIN —	6
7	— GREEN COAX DRAIN —	7
8	— BLUE COAX DRAIN —	8

P1	COLOR	P2
4	BROWN	4
11	BROWN/WHITE	11
12	RED	12
15	RED/WHITE	15
5	ORANGE	5
5	ORANGE/WHITE	5
13	YELLOW	13
10	YELLOW/WHITE	10
14	BLACK	14
10	BLACK/WHITE	10
SHIELD		SHIELD

- SPEC:
- CABLE UL2919 3COAX+5PAIR(28AWG) 100%AL DRAIN BRAID JACKET BLACK IN COLOR OD:9.0MM
 - CONNECTOR BLACK HDD15PIN MALE PIN9 REMOVED PIN GOLD PLATED
 - MOLDING SCREW 4-40UNC 4x49.5mm.
 - FERRITE CORE (Ø17.5*28.5*Ø10.5MM)
 - 100%METAL SHELL OF HDD15PIN CONNECTORS
 - MOLDING PVC BLACK IN COLOR.

THIRD ANGLE PROJECTION



GENERAL NOTES

DIMENSIONS ARE IN MM - DO NOT SCALE
 THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM



PRODUCT ID	MXTMMHQxxM_Diagram
DESCRIPTION	Coax High Resolution VGA Monitor Cable - HD15 M/M
DO NOT SCALE	SHEET: 1 OF: 1
	UPLOAD DATE: 12/9/2020

8 7 6 5 4 3 2 1