

## 3U 9in Deep Rackmount Locking Storage Drawer

SH39LK

DE: Bedienungsanleitung - [de.startech.com](http://de.startech.com)

FR: Guide de l'utilisateur - [fr.startech.com](http://fr.startech.com)

ES: Guía del usuario - [es.startech.com](http://es.startech.com)

IT: Guida per l'uso - [it.startech.com](http://it.startech.com)

NL: Gebruiksaanwijzing - [nl.startech.com](http://nl.startech.com)

PT: Guia do usuário - [pt.startech.com](http://pt.startech.com)



\*actual product may vary from photos

### Packaging Contents

- 1 x SH39LK Lockbox
- 2 x Key
- 5 x M5 Cabinet Screw
- 4 x M5 Cage Nut

### Installation

1. After unpacking the SH39LK lockbox, ensure that the swing door is closed and locked with the supplied keys, before attempting installation. You may also wish to ensure proper operation of the locking mechanism, before installation.
2. Determine where on the rack you will be placing the SH39LK lockbox. If using a square holed rack, install the included cage nuts onto the rack posts to match the mounting points on the SH39LK mounting brackets.
3. Place the lockbox against the front of the rack posts and secure it to the posts with the provided, M5 cabinet screws.

### Specifications

<b>Description</b>	3U Security Lockbox
<b>Color</b>	Black
<b>Materials</b>	SPCC (1.2 mm)
<b>Mounting Height</b>	3U
<b>External Dimensions (DxWxH)</b>	247.0 mm x 482.6 mm x 132.6 mm
<b>Net Weight</b>	4.1 kg
<b>Standards</b>	EIA-310C
<b>Certifications</b>	UL/CE

### Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. Regardless of any direct acknowledgement elsewhere in the body of this document, StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

### Technical Support

StarTech.com's lifetime technical support is an integral part of our commitment to provide industry-leading solutions. If you ever need help with your product, visit [www.startech.com/support](http://www.startech.com/support) and access our comprehensive selection of online tools, documentation, and downloads.

For the latest drivers/software, please visit [www.startech.com/downloads](http://www.startech.com/downloads)

### Warranty Information

This product is backed by a one year warranty.

In addition, StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

### Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.