





TOLERANCE: ±0.5mm



| ITEM. | DESCRIPTIONS | Q'TY |
|-------|-------------------------------------------|------|
| P6 | PUSH BUTTON | 1PCS |
| P5 | 2-PORT DP1.2 KVM SWITCH | 1PCS |
| P4 | 3.5mm STEREO PLUG MD TYPE/C:PANTONE 1775C | 2PCS |
| P3 | 3.5mm STEREO PLUG MD TYPE/C:PANTONE 358C | 2PCS |
| P2 | USB AM MD TYPE/C:BLACK | 2PCS |
| P1 | DisplayPort PLUG ASSY TYPE/C:BLACK | 2PCS |

THIRD ANGLE PROJECTION

GENERAL NOTES
 DIMENSIONS ARE IN MM - DO NOT SCALE
 THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM

| | |
|------------------|---------------------------------------------------------------|
| PRODUCT ID | SV211DPUA4K |
| DESCRIPTION | 2 Port USB 4K60Hz DisplayPort KVM Switch with Built-In Cables |
| REV: A | DO NOT SCALE |
| SHEET : 1 | OF: 1 |
| DATE: 04/27/2020 | |