


Electrical Test:
 1.100%Test(Open ,short ,miss wire)
 2.Contact Resistance: 3 ohm max.
 3.Insulation Resistance: 10M ohm Min.300V DC/10ms.



11	Low pressure molding compound	0.5	g
10	USB TYPE C~upper mater cover~Nickel Plated	1	pcs
9	USB TYPE C~lower mater cover~Nickel Plated	1	pcs
8	W=5MM 25u~Double conductive copper foil	0.012	m
7	45P Black PVC	3	g
6	LDPE	1	pcs
5	TYPEC~USB C Type Connector With~PCB+SMT~Nickel Plated	1	pcs
4	USB2.0 AM~Shell~Nickel Plated	16	g
3	USB2.0 AM Shell~Nickel Plated	3	g
2	USB2.0 AM Insulator White~PIN Gold plated	1	pcs
1	NO~UL30AWG(19/0.06TC)*2C+24AWG(26/0.1TC+250Dnylon)+3E(19/0.05TC+250Dnylon)+AB(16/9/0.06TC 95%TC)0D:3.0MM Black	1.03	m
NO	DESCRIPTION	Q'TY	UNIT

THIRD ANGLE PROJECTION

StarTech.com

GENERAL NOTES		PRODUCT ID	USB2AC1MR
DIMENSIONS ARE IN MM - DO NOT SCALE		DESCRIPTION	USB-A to USB-C Cable - Right-Angle - M/M - 1 m (3 ft.) - USB 2.0
THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM		DO NOT SCALE	SHEET: 1 OF: 1
		UPLOAD DATE: 11/26/2020	