






P1



- 1 1.PVC JACKET
- 2 2.CONDUCTOR
- 3 3.INSULATION
- 4 4.AL/MY
- 5 5.DRAIN WIRE
- 6 6.BRAID(ALUMINIUM MAGNESIUM ALLOY)



P2


PINOUT:

PAIR	P1	COLOR	P2
1	2	WHITE	2
	3	GREEN	3
	1	RED	1
	4	BLACK	4
	SHELL	DR+BR	SHELL

SPEC:

1. CABLE UL2725 1 PAIR 28AWG+2CONDUCTOR 24AWG DRAIN BRAID JACKET BLACK IN COLOR OD:4.4mm
2. CONNECTOR USB "A" TYPE 4PIN MALE SHELL NICKEL PLATED
3. CONNECTOR USB "B" TYPE 4PIN MALE SHELL NICKEL PLATED
4. MOLDING PVC BLACK IN COLOR.

THIRD ANGLE PROJECTION



GENERAL NOTES

DIMENSIONS ARE IN MM - DO NOT SCALE
 THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM

StarTech.com

PRODUCT ID	USB2HAB1		
DESCRIPTION	1 ft USB 2.0 A to B Cable - M/M		
DO NOT SCALE	SHEET: 1 OF: 1	UPLOAD DATE: 08/19/2020	