






P1



P2



- 1 1.PVC JACKET
- 2 2.CONDUCTOR
- 3 3.INSULATION
- 4 4.AL/MY
- 5 5.DRAIN WIRE
- 6 6.BRAID(ALUMINIUM MAGNESIUM ALLOY)




PINOUT:

P1	COLOR	P1
1	RED	1
4	BLACK	2

SPEC:

1. CABLE UL2725 28AWG*2C+ADB(BRAID:MAGNESIUM)
JACKET PVC BLACK IN COLOR OD:3.8MM
2. CONNECTOR: USB "A" TYPE 4PIN MALE SHELL NICKEL PLATED
3. CONNECTOR: DC TYPE $\phi 5.5 * \phi 2.5$ mm(L=23MM) SHELL NICKEL PLATED
4. MOLDING PVC BLACK IN COLOR.

THIRD ANGLE PROJECTION



GENERAL NOTES

DIMENSIONS ARE IN MM - DO NOT SCALE
THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM

StarTech.com

PRODUCT ID	USB2TYPEN2M		
DESCRIPTION	USB to 5.5mm Power Cable - Type N Barrel - 2m		
DO NOT SCALE	SHEET: 1 OF: 1	UPLOAD DATE: 08/31/2020	