

PIN ASSIGNMENT

P1	WIRE TYPE	P2	COLOR
1		1	RED
4		2	BLACK


SKU	LENGTH
USB2TYPEN1M	1000±30MM
USB2TYPEN2M	2000±35MM

NOTE:

1. OPEN/SHORT/INTERMITTENCE 100% TEST.
2. DIELECTRIC STRENGTH:200 VOLTS AC 2mA MAX/0.02S.
3. INSULATION RESISTANCE:300V DC/0.02SEC, 10MΩ MIN.
4. CONDUCTIVE RESISTANCE:3Ω MAX.

NO.	NAME	MATERIAL DESCRIPTION	QTY	UNITS
5	INNER MOLD	LD-PE	A/R	KG
4	OVER MOLD	PVC , COLOR:BLACK	A/R	KG
3	CONNECTOR	ø5.5 *ø2.5 DC PLUG,NICKEL PLATED BLACK INSULATION.	1	PCS
2	CONNECTOR	USB A/M (SOLDER TYPE) PIN: G/F, NICKEL PLATED FOR SHELL,WHITE INSULATION.	1	SET
1	CABLE	USB 2.0 UL2725 28#*1P+28#*2C+AL+D +B(16*3/0.12AL-M) OD:3.8mm BLACK PVC JACKET	A/R	M

THIRD ANGLE PROJECTION



GENERAL NOTES

DIMENSIONS ARE IN MM - DO NOT SCALE
 THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM

StarTech.com

PRODUCT ID	USB2TYPENxM
DESCRIPTION	USB to 5.5mm Power Cable - Type N Barrel
DO NOT SCALE	SHEET: 1 OF: 1
	UPLOAD DATE: 11/2/2021