

**PIN ASSIGNMENT**


P1	WIRE TYPE	P2	WIRE COLOR
PIN1		PIN1	RED
PIN2		PIN2	WHITE
PIN3		PIN3	GREEN
PIN4		PIN4	S
PIN5		PIN5	BLUE
PIN6		PIN6	YELLOW
PIN7		PIN7	DRAIN
PIN8		PIN8	PURPLE
PIN9		PIN9	ORANGE

**NOTES:**

- 1.OPEN/SHORT/INTERMITTENCE 100% TEST.
- 2.DIELECTRIC STRENGTH:200V AC 5mA/0.01S.
- 3.INSULATION RESISTANCE:300V DC/0.01S 10MΩ MIN.
- 4.CONDUCTIVE RESISTANCE:2Ω MAX.

5	IN MOLD	PE	/	KG
4	OVER MOLD	PVC 45P BLACK	/	KG
3	CONN	USB3.0 A/F SOLDER CONTACT:PIN G/F BLUE PLASTIC SHELL:NI-PLATED	1	SET
2	CONN	USB3.0 A/M SOLDER CONTACT:PIN G/F BLUE PLASTIC SHELL:NI-PLATED	1	SET
1	CABLE	USB3.0 CABLE,(30#*1P+D+AL)*2+30#*1P +24#*1C+S+AL,BLACK PVC JACKET,OD:4.5mm	A/R	PCS
No	PART NUMBER	MATERIAL DESCRIPTION	Q'TY	UNITS

THIRD ANGLE PROJECTION



**GENERAL NOTES**

DIMENSIONS ARE IN MM - DO NOT SCALE  
THIS DOCUMENT CONTAINS CONFIDENTIAL,  
PROPRIETARY INFORMATION THAT IS  
PROPERTY OF STARTECH.COM

**StarTech.com**

PRODUCT ID	USB3EXT6INBK
DESCRIPTION	USB 3.0 A-to-A Extension Cable - M/F - 6 in, Black
<b>DO NOT SCALE</b>	<b>SHEET: 1 OF: 1</b>
<b>UPLOAD DATE: 8/24/2021</b>	