


CABLE SECTION

USB3.0 AM	MCBM	COLOR
1	1	RED
2	2	WHITE
3	3	GREEN
4	5	BLACK
5	6	YELLOW
6	7	BLUE
7	8	DRAIN
8	9	ORANGE
9	10	PURPLE
SHELL	SHELL	BRAID

- ELECTRICAL PROPERTIES:
- 100% OPEN SHORT MIS-WIRE TEST
 - CONTACT RESISTANCE:100OHM.
 - INSULATION RESISTANCE:5MEGA OHM.
 - HIPOT TEST:300V/10MS.

THIRD ANGLE PROJECTION



NO.	DESCRIPTION	Q'TY	UNIT
4	55P PVC MOLDING BLUE IN COLOR	1	pcs
3	USB3.0 MICRO B TYPE MALE SHELL PLATED:NICKEL CONTACT:G/F	1	pcs
2	USB3.0 A TYPE MALE SHELL PLATED:NICKEL CONTACT:G/F	1	pcs
1	UL20276 (1P*28#+D+AL+Mya1r)*2C+1P*28#+2C*28#+AL+B OD:5.5±0.15mm BLUE IN COLOR	1	pcs

GENERAL NOTES
 DIMENSIONS ARE IN MM - DO NOT SCALE
 THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM

PRODUCT ID	USB3SAUB1
DESCRIPTION	1 ft SuperSpeed USB 3.0 Cable A to Micro B
DO NOT SCALE	SHEET: 1 OF: 1
	UPLOAD DATE: 08/13/2020