

## External V.92 56K USB Fax Modem

USB56KEM2

DE: Bedienungsanleitung - de.startech.com

FR: Guide de l'utilisateur - fr.startech.com

ES: Guía del usuario - es.startech.com

IT: Guida per l'uso - it.startech.com

NL: Gebruiksaanwijzing - nl.startech.com

PT: Guia do usuário - pt.startech.com

### Packaging Contents

- 1 x USB56KEM2 adapter
- 1 x RJ11 cable
- 1 x Driver CD
- 1 x Installation Guide

### System Requirements

- USB enabled computer system with available USB port
- Microsoft® Windows® 2000/XP/Server 2003/Vista/Server 2008 R2/7 (32/64-bit) or Apple® Mac OS® 10.5 or Linux kernel 2.6.18 or later

### Installation

1. Power on the computer system and boot into Windows
2. Connect the USB adapter into an available USB port. Windows will automatically detect the new hardware.
3. Insert the included CD into the computer's CD/DVD drive.
4. AutoPlay should launch the installation splash screen. If not, navigate to the CD via "My Computer" and run the setup.exe.
5. Select the Install Driver option and proceed with the installation.
6. Once complete, the drivers for the USB adapter should be installed.



### Verifying Installation

From the main desktop, right-click on "My Computer" ("Computer" in Vista/7), then select Manage. In the new Computer Management window, select Device Manager from the left window panel.

Double-click on the "Modems" option and a new device should be present.

## Specifications

<b>Bus Interface</b>	USB 2.0
<b>Chipset ID</b>	Agere/LSI SV92U2
<b>Connectors</b>	1 x RJ11 Female 1 x USB Type A Male
<b>LEDs</b>	1 x Power
<b>Supported Standards</b>	ITU-TV.92, V.90, V.34, V.32bis
<b>Maximum Data Transfer Rate</b>	Down: 56Kbps Up: 46Kbps Fax: 14.4Kbps
<b>Power Consumption</b>	0.1W
<b>Operating Temperature</b>	0°C - 70°C (32°F - 158°F)
<b>Storage Temperature</b>	-20°C - 85°C (-4°F - 185°F)
<b>Humidity</b>	5 - 95% RH
<b>Dimensions</b>	195.0mm x 32.0mm x 21.0mm
<b>Weight</b>	50g
<b>Compatible Operating Systems</b>	Windows® 2000/XP/Server 2003/Vista/ Server 2008 R2/7 (32/64-bit), Mac OS 10.5, Linux kernel 2.6.18 or later

### FCC Compliance Statement

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.

Consult the dealer or an experienced radio/TV technician for help.

### Use of Trademarks, Registered Trademarks, and other Protected Names & Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. Regardless of any direct acknowledgement elsewhere in the body of this document, StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

### Technical Support

StarTech.com's lifetime technical support is an integral part of our commitment to provide industry-leading solutions. If you ever need help with your product, visit [www.startech.com/support](http://www.startech.com/support) and access our comprehensive selection of online tools, documentation, and downloads.

### Warranty Information

This product is backed by a two year warranty.

In addition, StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only. StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

### Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.