

SKU	LENGTH
USBAUB50CMRA	500±30
USBAUB1MRA	1000±30
USBAUB2MRA	2000±35


PINOUT:

PAIR	P1	COLOR	P2
1PAIR	2	WHITE	2
	3	GREEN	3
2C	1	RED	1
	4	BLACK	5
SHELL		BRAID	SHELL

SPEC:

- CABLE UL2725 1 PAIR 30AWG+2C 24AWG+AL+D.W+BR  
JACKET PVC BLACK IN COLOR OD:3.5mm
- P1 CONNECTOR: USB "A" TYPE 4PIN MALE
- P2 CONNECTOR: MICRO USB "B" TYPE 5PIN MALE
- MOLDING PVC BLACK IN COLOR.

THIRD ANGLE PROJECTION



GENERAL NOTES

DIMENSIONS ARE IN MM - DO NOT SCALE  
THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM



PRODUCT ID	USBAUBxMRA
DESCRIPTION	Micro-USB Charge-and-Sync Cable M/M - Right-Angle Micro-USB - 30/24 AWG
<b>DO NOT SCALE</b>	<b>SHEET: 1 OF: 1</b>
<b>UPLOAD DATE: 10/13/2020</b>	