

- SPEC:**
- UL2725 28AWG*1P+28AWG*2C+AL+BRAID JACKET BEIGE IN COLOR OD:3.0MM
 - CONNECTOR USB A TYPE 4PIN FEMALE SHELL NICKEL PLATED
 - HOUSING 2*5PIN PH:2.54MM KEY TYPE BLUE COLOR
 - POWER BRACKET
 - SCREW 4-40UNC
NUTS 4-40UNC
 - BLACK SHRINK TUBE
 - MOLDING PVC BEIGE IN COLOR
 - CABLE TIE WHITE IN COLOR


- ELECTRIC TESTING:**
- 100% OPEN & SHORT TESTING
 - INSULATION RESISTANCE: $\geq 10M\Omega$
 - CONDUCTOR RESISTANCE: $\leq 5M\Omega$
 - VOLTAGE: 300V DC/1Sec

PINOUT:

P1	COLOR	P3	P2	COLOR	P5
1	RED	1	1	RED	1
3	WHITE	2	3	WHITE	2
5	GREEN	3	5	GREEN	3
7	BLACK+DRAIN	4+SHELL	7	BLACK+DRAIN	4+SHELL

P1	COLOR	P4	P2	COLOR	P6
2	RED	1	2	RED	1
4	WHITE	2	4	WHITE	2
6	GREEN	3	6	GREEN	3
8	BLACK+DRAIN	4+SHELL	8	BLACK+DRAIN	4+SHELL

THIRD ANGLE PROJECTION



GENERAL NOTES

DIMENSIONS ARE IN MM - DO NOT SCALE
 THIS DOCUMENT CONTAINS CONFIDENTIAL, PROPRIETARY INFORMATION THAT IS PROPERTY OF STARTECH.COM



PRODUCT ID	USBPLATE4		
DESCRIPTION	4 Port USB A Female Slot Plate Adapter		
REV: A	DO NOT SCALE	SHEET : 1 OF: 1	DATE: 05/27/2020